

16th of September 2021

Swissphotonics talk

Moirés by superposition of cylindrical microlens gratings

Dr Romain Rossier
CEO and Co-founder

EPFL Innovation Park
Building D
CH-1015 Ecublens

T +41 78 664 36 44
E romain.rossier@innoview.ch
W www.innoview.ch



Summary

Moiré principles

- Classical Moiré fringes

Categories of “shape” moirés

- 1D and 2D Moirés, Level-line Moiré
- Design possibilities


Applications

- Rectilinear and spiral revealing layers
- Parallax with micro lenses
- Metallic deposition
- Lenslet extensions




Classical Moiré fringes


10 degrees



Line grating



Square grid



Dot screen







Period and orientation of the moiré

[Righi 1887], [Tollenaar 1945], [Bryngdahl 1974]



Moiré analysis

multiplication in image space \leftrightarrow convolution in Fourier space



See book: The Theory of the Moiré Phenomenon, I. Amidror, Kluwer



1D Moiré



1D Moiré

Revealing layer


- Repeated 1D lines at a certain period
- Cylindrical micro lenses

Base layer

- Repeated structures at a different period


Animation

- Movement of the revealed shape (logo, text) **by displacing** the revealing layer on top of the base layer
- Aesthetic animations (rotation, spiral, radial)






Sampling of the base layer






Base layer transformation: circle






Spiral revealing layer





Parallax with micro lenses





Lenslet: lenses on both sides







2D Moiré



2D moiré: patterned metal base and spherical lenses revealer



Spherical lenses



Nominal lens diameter $D=185\ \mu\text{m}$




Viewing angle at 0 degree



Viewing angle at 10 degrees



2D Moiré: metallic base and lenses





Level-Line Moiré




Level-line Moiré simple shape

Animation

— Shape is beating (not moving like 1D/2D Moirés)



Heart profile





Parallax: distance between base and revealer





Elevation profile of Michelangelo's David





Lenslet: surface effect





Processes of fabrication

Base and revealing layers

- Metallic deposition
- Laser engraving
- PVD process
- Transparent films
- Micro lenses

Animation

- Parallax with distance between base layer and revealer, e.g. 1mm
- Parallax with micro lenses

THANK YOU